



VT4430

by Burndy
Catalog ID: VT4430

Prop 65 Notice

V Style Connectors

Product Details

General

Application	Substation
Connector Type	T-Connector
Installation Torque Recommended in-lb	3 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Trade Name	VARITAP™
Type	Bolted Tees
UPC	781810448892
UPC 12 Digit	7818104488922

Dimensions

Dimension - Height inch	2.88 in
Dimension - L Length Overall mm	108 mm
Dimension - Length Overall inch	4.25 in
Dimension - Width inch	1.94 in
Dimension - Width mm	49 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Cable to Cable
Conductor - Copper Solid Tap	2/0 AWG;3/0 AWG;4/0 AWG
Conductor - Copper Solid Tap Range	2/0 AWG-4/0 AWG
Conductor - Copper Str Run	750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil
Conductor - Copper Str Run Range	750 kcmil-1000 kcmil
Conductor - Copper Str Tap	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil

Conductor - Copper Str Tap Range	1/0 -300 kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Run • CU C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)