



VT4840

by Burndy
Catalog ID: VT4840

Prop 65 Notice

V Style Connectors

Product Details

General

Application	Substation
Connector Type	T-Connector
Installation Torque Recommended in-lb	5.8 LBS/in
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Plated	N
Plating Type	Unplated
Trade Name	VARITAP™
Type	Bolted Tees
UPC	781810234549
UPC 12 Digit	7818102345499

Dimensions

Dimension - Height inch	4.25 in
Dimension - L Length Overall mm	143 mm
Dimension - Length Overall inch	5.63 in
Dimension - Width inch	2.63 in
Dimension - Width mm	67 mm

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Cable to Cable
Conductor - Copper Str Run	1500 kcmil;1600 kcmil;1750 kcmil;2000 kcmil
Conductor - Copper Str Run Range	1500 kcmil-2000 kcmil
Conductor - Copper Str Tap	500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil
Conductor - Copper Str Tap Range	500 kcmil-800 kcmil

Conductor Type	<ul style="list-style-type: none">• CU C Str-Run• CU C Str-Tap
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)