



WAD1029

by Burndy
Catalog ID: WAD1029

Prop 65 Notice

MAX RANGE: .398 - .502 ACSR: 1/0 (6/1), 2/0 (6/1), 3/0 (6/1) AAC: 1/0, 2/0, 3/0 29 kV, 110 BIL

Product Details

General

Insulator Type	Silicon
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810644737
UPC 12 Digit	7818106447377

Electrical Ratings

Current Rating	900 A
----------------	-------

Conductor Related

Conductor - AAAC 5005 Size	30.58 (7) kcmil
Conductor - AAAC 5005 Size Range	30.58 (7) kcmil
Conductor - AAAC 6201 Size	30.58 (7) kcmil
Conductor - AAAC 6201 Size Range	30.58 (7) kcmil
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG-3/0 (6/1) Pigeon AWG
Conductor - AL Str Size	1/0 AWG;2/0 AWG;3/0 AWG
Conductor - AL Str Size Range	1/0 AWG-3/0 AWG
Conductor Type	<ul style="list-style-type: none"> • AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)