



## WAD33635

by Burndy  
Catalog ID: WAD33635

Prop 65 Notice

MAX RANGE: .642 - .723 ACSR: 266.8 (26/7), 336.4 (18/1), (26/7) AAC:  
336, 350, 397.5, 477 COMPACT 35 kV, 200 BIL

### Product Details

#### General

Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810462157
UPC 12 Digit	7818104621577

#### Dimensions

Dimension - B Length fraction	22-2/5 in
Dimension - B Length inch	22.4 in
Dimension - Length Overall inch	54 in

#### Electrical Ratings

Current Rating	900 A
----------------	-------

#### Conductor Related

Conductor - AAAC 5005 Size	312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 5005 Size Range	312.8 (19) kcmil-394.5 (19) kcmil
Conductor - AAAC 6201 Size	312.8 (19) kcmil;394.5 (19) kcmil
Conductor - AAAC 6201 Size Range	312.8 (19) kcmil-394.5 (19) kcmil
Conductor - ACSR Str Size	266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil
Conductor - ACSR Str Size Range	266.8 (26/7) Owl kcmil-336.4 (30/7) Oriole kcmil
Conductor - AL Str Size	336 kcmil;350 kcmil;397 kcmil
Conductor - AL Str Size Range	336 kcmil-397 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AAAC C 5005-Size</li> <li>• AAAC C 6201-Size</li> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)