



WAD4015

by Burndy
Catalog ID: WAD4015

Prop 65 Notice

MAX RANGE: .522 - .609 ACSR: 4/0 (6/1), 266.8 (18/1) AAC: 4/0, 250, 266.8 (7 STR, 19 STR), 336 COMPACT 15 kV, 110 BIL

Product Details

General

Insulator Type	Silicon
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810489161
UPC 12 Digit	7818104891611

Electrical Ratings

Current Rating	900 A
----------------	-------

Conductor Related

Conductor - AAAC 5005 Size	30.58 (7) kcmil
Conductor - AAAC 5005 Size Range	30.58 (7) kcmil
Conductor - AAAC 6201 Size	30.58 (7) kcmil
Conductor - AAAC 6201 Size Range	30.58 (7) kcmil
Conductor - ACSR Str Size	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil
Conductor - ACSR Str Size Range	4/0 (6/1) Penguin AWG-266.8 (18/1) Waxwing kcmil
Conductor - AL Str Size	4/0 AWG;250 kcmil;266 kcmil
Conductor - AL Str Size Range	4/0 AWG-266 kcmil
Conductor Type	<ul style="list-style-type: none"> • AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)