



## WAD435NS

by Burndy  
Catalog ID: WAD435NS

In-Line W/O switch

### Product Details

#### General

Insulator Type	Silicon
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
UPC	781810540817
UPC 12 Digit	7818105408177

#### Electrical Ratings

Current Rating	900 A
----------------	-------

#### Conductor Related

Conductor Type	<ul style="list-style-type: none"> <li>• AAAC C 5005-Size</li> <li>• AAAC C 6201-Size</li> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>
----------------	--

#### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

#### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)