



WAD47729

by Burndy
Catalog ID: WAD47729

Prop 65 Notice

MAX RANGE: .741 - .814 29 kV, 150 BIL ACSR: 336.4 (30/7), (26/7), (30/7), 397.5 (ALL STR), 477 (18/1) AAC: 477 (19 STR, 37 STR), 500 (19 STR, 37 STR), 556 COMPACT

Product Details

General

Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810462171
UPC 12 Digit	7818104621711

Dimensions

Dimension - B Length fraction	17-9/10 in
Dimension - B Length inch	17.9 in
Dimension - Length Overall inch	48 in

Electrical Ratings

Current Rating	900 A
----------------	-------

Conductor Related

Conductor - AAAC 5005 Size	465.4 (19) kcmil
Conductor - AAAC 5005 Size Range	465.4 (19) kcmil
Conductor - AAAC 6201 Size	465.4 (19) kcmil
Conductor - AAAC 6201 Size Range	465.4 (19) kcmil
Conductor - ACSR Str Size	397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil
Conductor - ACSR Str Size Range	397.5 (18/1) Chickadee kcmil-477.0 (18/1) Pelican kcmil
Conductor - AL Str Size	450 kcmil;477 kcmil;500 kcmil
Conductor - AL Str Size Range	450 kcmil-500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)