



WAD55615

by Burndy
Catalog ID: WAD55615

Prop 65 Notice

MAX RANGE: .846 - .883 ACSR: 477 (24/7), (26/7), (30/7), 556.5 (18/1)
AAC: 556 (19 STR, 37 STR) 15 kV, 110 BIL

Product Details

General

Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810462195
UPC 12 Digit	7818104621955

Dimensions

Dimension - B Length fraction	13-2/5 in
Dimension - B Length inch	13.4 in
Dimension - Length Overall inch	45 in

Electrical Ratings

Current Rating	900 A
----------------	-------

Conductor Related

Conductor - AAAC 5005 Size	559.5 (19) kcmil
Conductor - AAAC 5005 Size Range	559.5 (19) kcmil
Conductor - AAAC 6201 Size	559.5 (19) kcmil
Conductor - AAAC 6201 Size Range	559.5 (19) kcmil
Conductor - ACSR Str Size	477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil
Conductor - ACSR Str Size Range	477.0 (24/7) Flicker kcmil-477. (30/7) Hen kcmil
Conductor - AL Str Size	556 kcmil
Conductor - AL Str Size Range	556 kcmil
Conductor Type	<ul style="list-style-type: none"> • AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)