



WAD795-15

by Burndy
Catalog ID: WAD795-15

Prop 65 Notice

MAX RANGE: .953 - 1.040 ACSR: 556 (24/7), (26/7), (30/7) 795 (36/1)
AAC: 795 (37 STR, 61 STR) 15 kV, 110 BIL

Product Details

General

Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810489178
UPC 12 Digit	7818104891788

Dimensions

Dimension - B Length fraction	13-2/5 in
Dimension - B Length inch	13.4 in
Dimension - Length Overall inch	45 in

Electrical Ratings

Current Rating	900 A
----------------	-------

Conductor Related

Conductor - AAAC 5005 Size	740.8 (37) kcmil
Conductor - AAAC 5005 Size Range	740.8 (37) kcmil
Conductor - AAAC 6201 Size	740.8 (37) kcmil
Conductor - AAAC 6201 Size Range	740.8 (37) kcmil
Conductor - ACSR Str Size	556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil;605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil
Conductor - ACSR Str Size Range	556.5 (26/7) Dove kcmil-636 (26/7) Grosbeak kcmil
Conductor - AL Str Size	795 kcmil
Conductor - AL Str Size Range	795 kcmil
Conductor Type	<ul style="list-style-type: none"> • AAAC C 5005-Size • AAAC C 6201-Size • ACSR C Str-Size • AL C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)