



## WAD795-35

by Burndy  
Catalog ID: WAD795-35

Prop 65 Notice

MAX RANGE: .953 - 1.040 ACSR: 556 (24/7), (26/7), (30/7) 795 (36/1)  
AAC: 795 (37 STR, 61 STR) 15 kV, 110 BIL

## Product Details

### General

Insulator Type	Silicon
Material	Aluminum Alloy
Rating - Body Strength	10000 lbs
Rating - Pulling Eye Strength	6000 lbs
Trade Name	WEJTAP™
UPC	781810489192
UPC 12 Digit	7818104891922

### Dimensions

Dimension - B Length fraction	22-2/5 in
Dimension - B Length inch	22.4 in
Dimension - Length Overall inch	54 in

### Electrical Ratings

Current Rating	900 A
----------------	-------

### Conductor Related

Conductor - AAAC 5005 Size	740.8 (37) kcmil
Conductor - AAAC 5005 Size Range	740.8 (37) kcmil
Conductor - AAAC 6201 Size	740.8 (37) kcmil
Conductor - AAAC 6201 Size Range	740.8 (37) kcmil
Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil;605 (24/7) Peacock kcmil;605 (26/7) Squab kcmil;605 (30/19) Teal kcmil;636 (24/7) Rook kcmil;636 (26/7) Grosbeak kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-636 (26/7) Grosbeak kcmil
Conductor - AL Str Size	795 kcmil
Conductor - AL Str Size Range	795 kcmil
Conductor Type	<ul style="list-style-type: none"> <li>• AAAC C 5005-Size</li> <li>• AAAC C 6201-Size</li> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)