


# WCB10

by Burndy  
Catalog ID: WCB10

Prop 65 Notice

Wejtap Assembly , Installed With Blue Booster,Run:.482-.316,  
Tap:.437-.257.

Features: WEJTAP Connectors Use An Aluminum Alloy Wedge That Is Power-Driven Between The Run And The Tap Cables Locking Them Into A C Shaped Tempered Aluminum Alloy Spring-Body, The Spring-Body Maintains Consistent Pressure Throughout The Life Of The Connection To Ensure Reliability During Severe Electrical And Climatic Conditions, The Wedges Wiping Action Combined With Factory Installed PENTX 1530 Provides Superior Contact Integrity, The Wedge Is Automatically Locked Onto The Spring-Body By A Skiving Action Produced By A Lance At The Forward End Of The WEJTAP Installation Tool, Installed With Blue Booster, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range: 0.795 - 0.621 IN, Cable Diameter Range (run): 0.482 - 0.316 IN, Cable Diameter Range (tap): 0.437 - 0.257 IN, Conductor Size (run - Mm): 8 - 12 SQ-MM, Conductor Size (tap - Mm): 7 - 11 SQ-MM, Installation Tool: WTRB, Booster: WPBB Box 25, Color Code: Blue



## Product Details

### General

Application	For use in tap applications using large run and tap conductor sizes
Sub Brand	WEJTAP
Type	Wejtap Connector
UPC	781810872451

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)