



## WCB16

by Burndy  
Catalog ID: WCB16

Prop 65 Notice

Wejtap connector installed with blue booster, .568-.364 (Run).

Features: With Blue Power Booster, ANSI Class AA, Color Code: Blue, Conductor Size (tap - Mm): 5 - 7 SQ-MM, Booster: WPBB Box 25, Booster Color: Blue, Installation Tool: WTRB Tool, Cable Diameter Range (run): 0.364 - 0.568 IN, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (tap): 0.204 - 0.258 IN, Conductor Size (run - Mm): 9 - 14 SQ-MM

## Product Details

### General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810872758
UPC 12 Digit	7818108727588

### Dimensions

Dimension - F Width Center to Center inch	1.64 in
Dimension - G inch	1.04 in

### Conductor Related

Conductor - ACSR Str Run	1/0 (6/1) Raven;2/0 (6/1) Quail;3/0 (6/1) Pigeon;4/0 (6/1) Penquin
Conductor - ACSR Str Run Range	1/0 (6/1) Raven-4/0 (6/1) Penquin
Conductor - ACSR Str Tap	5 (6/1) Thrush;4 (6/1) Swan;4 (7/1) Swanate
Conductor - ACSR Str Tap Range	5 (6/1) Thrush-4 (7/1) Swanate
Conductor - AL Str Run	1/0;2/0;3/0;4/0
Conductor - AL Str Run Range	1/0-4/0
Conductor - AL Str Tap	4
Conductor - AL Str Tap Range	4

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	25
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)