



WCB17PB

by Burndy
Catalog ID: WCB17PB

Prop 65 Notice

Wejtap connector installed with blue booster, .364-.568 (Run), .257-.464 (Tap)

Product Details

General

Color	Blue
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810870075
UPC 12 Digit	7818108700755

Dimensions

Dimension - F Width Center to Center inch	1.64 in
Dimension - G inch	1.04 in

Conductor Related

Conductor - ACSR Str Run	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Run Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap	4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Tap Range	4 (7/1) Swanate AWG-3/0 (6/1) Pigeon AWG
Conductor - AL Str Run	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - AL Str Tap Range	3 AWG-3/0 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	NC

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)