



## WCB18

by Burndy  
Catalog ID: WCB18

Prop 65 Notice

Wejtap connector installed with blue booster, .364-.568 (Run), .572-.364 (Tap).

Features: With Blue Power Booster, ANSI Class AA, Color Code: Blue, Conductor Size (tap - Mm): 9 - 15 SQ-MM, Installation Tool: WTRB Tool, Booster Color: Blue, Booster: WPBB Box 25, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (run): 0.364 - 0.568 IN, Cable Diameter Range (tap): 0.364 - 0.572 IN, Conductor Size (run - Mm): 9 - 14 SQ-MM

## Product Details

### General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810872857
UPC 12 Digit	7818108728577

### Dimensions

Dimension - F Width Center to Center inch	1.64 in
Dimension - G inch	1.04 in

### Conductor Related

Conductor - ACSR Str Run	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Run Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap	1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG;4/0 (6/1) Penquin AWG
Conductor - ACSR Str Tap Range	1/0 (6/1) Raven AWG-4/0 (6/1) Penquin AWG
Conductor - AL Str Run	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Run Range	1/0 AWG-4/0 AWG
Conductor - AL Str Tap	1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG
Conductor - AL Str Tap Range	1/0 AWG-4/0 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)