



## WCB25

by Burndy  
Catalog ID: WCB25

Prop 65 Notice

Wejtap Assembly, 0.650-0.532 (Run), 0.562-0.364 (Tap), Installed With Blue Booster

## Product Details

### General

|                |               |
|----------------|---------------|
| Connector Type | Tap           |
| Material       | Aluminum      |
| Trade Name     | WEJTAP™       |
| UPC            | 781810873205  |
| UPC 12 Digit   | 7818108732055 |

### Dimensions

|   |         |
|---|---------|
| Dimension - F Width Center to Center inch | 1.89 in |
| Dimension - G inch                        | 1.05 in |

### Conductor Related

|                                |   |
|--------------------------------|---|
| Conductor - ACSR Str Run       | 4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil |
| Conductor - ACSR Str Run Range | 4/0 (6/1) Penguin AWG-266.8 (26/7) Partridge kcmil  |
| Conductor - ACSR Str Tap       | 1/0 (6/1) Raven AWG;2/0 (6/1) Quail AWG;3/0 (6/1) Pigeon AWG  |
| Conductor - ACSR Str Tap Range | 1/0 (6/1) Raven AWG-3/0 (6/1) Pigeon AWG  |
| Conductor - AL Str Run         | 250 kcmil;266 kcmil;300 kcmil   |
| Conductor - AL Str Run Range   | 250 kcmil-300 kcmil   |
| Conductor - AL Str Tap         | 1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG   |
| Conductor - AL Str Tap Range   | 1/0 AWG-4/0 AWG   |

### Certifications and Compliance

|                                    |    |
|------------------------------------|----|
| Certification - CSA Approved       | No |
| Certification - ETL                | No |
| Certification - UL Recognized      | No |
| Certification - cULus              | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed                          | No |

### Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)