



## WCB40

by Burndy  
Catalog ID: WCB40

Prop 65 Notice

Wejtap connector installed with blue booster, .603-.684 (Run), .162-.204 (Tap)

## Product Details

### General

Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810873403
UPC 12 Digit	7818108734033

### Dimensions

Dimension - F Width Center to Center inch	2 in
Dimension - G inch	1.1 in

### Conductor Related

Conductor - ACSR Str Run	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG
Conductor - AL Str Run	300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Run Range	300 kcmil-350 kcmil
Conductor - AL Str Tap	8 AWG;6 AWG
Conductor - AL Str Tap Range	8 AWG-6 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)