



## WCB41PB

by Burndy  
Catalog ID: WCB41PB

Prop 65 Notice

WEJTAP Connector , 0.684 - 0.600 (Run), 0.258 - 0.204 (Tap), With Blue Power Booster Assembly

## Product Details

### General

Color	Blue
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810870204
UPC 12 Digit	7818108702044

### Dimensions

Dimension - F Width Center to Center inch	2 in
Dimension - G inch	1.1 in

### Conductor Related

Conductor - ACSR Str Run	266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Run Range	266.8 (18/1) Waxwing kcmil-336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Tap	5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG
Conductor - ACSR Str Tap Range	5 (6/1) Thrush AWG-4 (7/1) Swanate AWG
Conductor - AL Str Run	300 kcmil;336 kcmil;350 kcmil
Conductor - AL Str Run Range	300 kcmil-350 kcmil
Conductor - AL Str Tap	4 AWG
Conductor - AL Str Tap Range	4 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	NC

### Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)