



WCR30

by Burndy
Catalog ID: WCR30

Prop 65 Notice

Wejtap Assembly , Installed With Red Booster, Sum of Diameters: .649 (Max), .516 (Min).

Features: Without Red Power Booster, ANSI Class AA, Color Code: Red, Conductor Size (tap - Mm): 5 - 8 SQ-MM, Booster: WPBR Box 25, Installation Tool: WTRB Tool, Cable Diameter Range (run): 0.257 - 0.398 IN, Conductor Type: Run: AAC, Tap: AAC, Copper, Cable Diameter Range (tap): 0.206 - 0.325 IN, Conductor Size (run - Mm): 7 - 10 SQ-MM

Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Color	Red
Connector Type	Tap
Material	Copper
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810872055
UPC 12 Digit	7818108720555

Dimensions

Dimension - F Width Center to Center inch	1.40 in
Dimension - G inch	0.92 in

Conductor Related

Conductor - ACSR Str Run	4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG;1 (6/1) Robin AWG;1/0 (6/1) Raven AWG
Conductor - ACSR Str Run Range	4 (7/1) Swanate AWG-1/0 (6/1) Raven AWG
Conductor - ACSR Str Tap	5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Tap Range	5 (6/1) Thrush AWG-2 (7/1) Sparate AWG
Conductor - AL Str Run	2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Run Range	2 AWG-1/0 AWG
Conductor - AL Str Tap	4 AWG;3 AWG;2 AWG
Conductor - AL Str Tap Range	4 AWG-2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)