

WCY103PB

by Burndy
Catalog ID: WCY103PB

Prop 65 Notice

WEJTAP Connector, 1.302 - 1.242 (Run), 1.302 - 1.242 (Tap), With Yellow Power Booster Assembly



Product Details

General

| | |
|----------------|---------------|
| Color | Yellow |
| Connector Type | Tap |
| Material | Copper |
| Trade Name | WEJTAP™ |
| UPC | 781810034217 |
| UPC 12 Digit | 7818100342177 |

Dimensions

| | |
|---|---------|
| Dimension - F Width Center to Center inch | 3.5 in |
| Dimension - G inch | 2.04 in |

Conductor Related

| | |
|--------------------------------|--|
| Conductor - ACSR Str Run | 1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil |
| Conductor - ACSR Str Run Range | 1033.5 (54/7) Curlew kcmil-1272 (54/19) Pheasant kcmil |
| Conductor - ACSR Str Tap | 1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil |
| Conductor - ACSR Str Tap Range | 1033.5 (54/7) Curlew kcmil-1272 (54/19) Pheasant kcmil |
| Conductor - AL Str Run | 1100 kcmil;1113 kcmil;1192 kcmil;1200 kcmil;1250 kcmil;1272 kcmil;1300 kcmil |
| Conductor - AL Str Run Range | 1100 kcmil-1300 kcmil |
| Conductor - AL Str Tap | 1100 kcmil;1113 kcmil;1192 kcmil;1200 kcmil;1250 kcmil;1272 kcmil;1300 kcmil |
| Conductor - AL Str Tap Range | 1100 kcmil-1300 kcmil |
| Conductor Type | <ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | NC |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 5 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)