

WCY106

by Burndy
Catalog ID: WCY106

Aluminum Overhead Wedge Tap Connector, 1.302 Dia. To 1.242 Dia. (Run),
1.116 Dia. To 1.016 Dia. (Tap)



Product Details

General

Connector Type	Tap
Material	Copper
Trade Name	WEJTAP™
UPC	781810057032
UPC 12 Digit	7818100570322

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	2.04 in

Conductor Related

Conductor - ACSR Str Run	1033.5 (54/7) Curlew kcmil;1113 (54/19) Finch kcmil;1192.5 (45/7) Bunting kcmil;1192.5 (54/19) Grackle kcmil;1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Run Range	1033.5 (54/7) Curlew kcmil-1272 (54/19) Pheasant kcmil
Conductor - ACSR Str Tap	636 (30/19) Egret kcmil;666.6 (24/7) Flamingo kcmil;715.5 (54/7) Crow kcmil;715.5 (24/7) Stilt kcmil;715.5 (26/7) Starling kcmil;715.5 (30/19) Redwing kcmil;795 (54/7) Condor kcmil;795 (26/7) Drake kcmil;795 (30/19) Mallard kcmil
Conductor - ACSR Str Tap Range	636 (30/19) Egret kcmil-795 (30/19) Mallard kcmil
Conductor - AL Str Run	1100 kcmil;1113 kcmil;1192 kcmil;1200 kcmil;1250 kcmil;1272 kcmil;1300 kcmil
Conductor - AL Str Run Range	1100 kcmil-1300 kcmil
Conductor - AL Str Tap	750 kcmil;795 kcmil;800 kcmil;874 kcmil;900 kcmil
Conductor - AL Str Tap Range	750 kcmil-900 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)