

# WCY110

by Burndy  
Catalog ID: WCY110

Aluminum Overhead Wedge Tap Connector, 1.302 Dia. To 1.242 Dia. (Run),  
0.877 Dia. To 0.777 Dia. (Tap)



## Product Details

### General

Connector Type	Tap
Material	Copper
Trade Name	WEJTAP™
UPC	781810211113
UPC 12 Digit	7818102111133

### Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	2.04 in

### Conductor Related

Conductor - ACSR Str Run	1033.5 (54/7) Curlew;1113 (54/19) Finch;1272 (54/19) Pheasant
Conductor - ACSR Str Run Range	1033.5 (54/7) Curlew-1272 (54/19) Pheasant
Conductor - ACSR Str Tap	397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur;477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen
Conductor - ACSR Str Tap Range	397.5 (24/7) Brant-477.0 (30/7) Hen
Conductor - AL Str Run	1100;1113;1192.5;1200;1272.2;1300
Conductor - AL Str Run Range	1100-1300
Conductor - AL Str Tap	450;477;500;550;556.5
Conductor - AL Str Tap Range	450-556.5

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)