

# WCY114PB

by Burndy  
Catalog ID: WCY114PB

Prop 65 Notice

CONN ANSI CL:AA RUS



## Product Details

### General

Color	Yellow
Connector Type	Tap
Material	Copper
UPC	781810094518
UPC 12 Digit	7818100945188

### Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	2.04 in

### Conductor Related

Conductor - ACSR Str Run	1033.5 (54/7) Curlew;1113 (54/19) Finch;1272 (54/19) Pheasant
Conductor - ACSR Str Tap	2/0 (6/1) Quail;3/0 (6/1) Pigeon;4/0 (6/1) Penquin;80 (8/1) Grouse;101.8 (12/7) Petrel;110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;211.3 (12/7) Cochin;203.2 (16/9) Brahma;266.8 (18/1) Waxwing
Conductor - AL Str Run	1100;1113;1192.5;1200;1272.2;1300;1351.5;1400
Conductor - AL Str Tap	3/0;4/0;250;266.8
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)