



# WCY48

by Burndy  
Catalog ID: WCY48

Prop 65 Notice

Wejtap connector installed with yellow booster, .537-.750 (Run), .162-.204 (Tap)

## Product Details

### General

Connector Type	Tap
Material	Copper
Trade Name	WEJTAP™
UPC	781810873809
UPC 12 Digit	7818108738099

### Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.37 in

### Conductor Related

Conductor - ACSR Str Run	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil
Conductor - ACSR Str Run Range	4/0 (6/1) Penguin AWG-397.5 (26/7) Ibis kcmil
Conductor - ACSR Str Tap	6 (6/1) Turkey AWG;5 (6/1) Thrush AWG
Conductor - ACSR Str Tap Range	6 (6/1) Turkey AWG-5 (6/1) Thrush AWG
Conductor - AL Str Run	4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil
Conductor - AL Str Run Range	4/0 AWG-450 kcmil
Conductor - AL Str Tap	8 AWG;6 AWG;4 AWG
Conductor - AL Str Tap Range	8 AWG-4 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)