

WCY55

by Burndy
Catalog ID: WCY55

Prop 65 Notice

Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.370 (Max), 1.140 (Min).

Features: With Yellow Power Booster, ANSI Class AA, Conductor Size (tap - Mm): 13 - 18 SQ-MM, Installation Tool: WTRB, WTY Tool, Color Code: Yellow, Booster Color: Yellow, Booster: WPBY Box 25, Conductor Type: Run: AAC, Tap: AAC, Copper, Cable Diameter Range (run): 0.537 - 0.75 IN, Conductor Size (run - Mm): 14 - 19 SQ-MM, Cable Diameter Range (tap): 0.499 - 0.714 IN



Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Copper
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810874158
UPC 12 Digit	7818108741588

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.37 in

Conductor Related

Conductor - ACSR Str Run	4/0 (6/1) Penguin;80 (8/1) Grouse;101.8 (12/7) Petrel;110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;211.3 (12/7) Cochin;203.2 (16/9) Brahma;266.8 (18/1) Waxwing;266.8 (26/7) Owl;266.8 (26/7) Partridge;300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis
Conductor - ACSR Str Run Range	4/0 (6/1) Penguin-397.5 (26/7) Ibis
Conductor - ACSR Str Tap	2/0 (6/1) Quail;3/0 (6/1) Pigeon;4/0 (6/1) Penguin;80 (8/1) Grouse;101.8 (12/7) Petrel;110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;211.3 (12/7) Cochin;203.2 (16/9) Brahma;266.8 (18/1) Waxwing;266.8 (26/7) Owl;266.8 (26/7) Partridge;300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet
Conductor - ACSR Str Tap Range	2/0 (6/1) Quail-336.4 (26/7) Linnet
Conductor - AL Str Run	4/0;250;266.8;300;336.4;350;397.5;400;450
Conductor - AL Str Run Range	4/0-450
Conductor - AL Str Tap	3/0;4/0;250;266.8;300;336.4;350;397.5
Conductor - AL Str Tap Range	3/0-397.5

Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Run• AL C Str-Run• ACSR C Str-Tap• AL C Str-Tap
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)