

# WCY59

by Burndy  
Catalog ID: WCY59

Prop 65 Notice

Wejtap Connector With Power Booster Assembly, 12.63 IN L, 6.38 IN W, 0.666-0.893 (Run), 0.162-0.199(Tap), Installed With Yellow Booster.

Features: With Yellow Power Booster, ANSI Class AA, Booster: WPBY Box 25, Installation Tool: WTRB Tool, Booster Color: Yellow, Conductor Size (tap - Mm): 4 - 5 SQ-MM, Color Code: Yellow, Cable Diameter Range (run): 0.666 - 0.893 IN, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (tap): 0.162 - 0.199 IN, Conductor Size (run - Mm): 17 - 23 SQ-MM



## Product Details

### General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Copper
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810874356
UPC 12 Digit	7818108743566

### Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.53 in

### Conductor Related

Conductor - ACSR Str Run	300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant;397.5 (26/7) Ibis;397.5 (30/7) Larkspur;477.0 (18/1) Pelican;477.0 (24/7) Flicker;477.0 (26/7) Hawk;477.0 (30/7) Hen;556.5 (24/7) Parakeet
Conductor - ACSR Str Run Range	300.0 (26/7) Ostrich-556.5 (24/7) Parakeet
Conductor - ACSR Str Tap	6 (6/1) Turkey
Conductor - ACSR Str Tap Range	6 (6/1) Turkey
Conductor - AL Str Run	336.4;350;397.5;400;450;477;500;550;556.5;600
Conductor - AL Str Run Range	336.4-600
Conductor - AL Str Tap	6;4
Conductor - AL Str Tap Range	6-4
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	10
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)