

WCY60

by Burndy
Catalog ID: WCY60

Prop 65 Notice

Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.854 (Max), 1.686 (Min).

Features: With Yellow Power Booster, ANSI Class AA, Color Code: Yellow, Installation Tool: WTY Tool, Booster: WPBY Box 25, Conductor Size (tap - Mm): 18 - 24 SQ-MM, Booster Color: Yellow, Cable Diameter Range (run): 0.722 - 0.95 IN, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Conductor Size (run - Mm): 18 - 24 SQ-MM, Cable Diameter Range (tap): 0.722 - 0.95 IN



Product Details

General

| | |
|----------------|---------------------------------------------------------------------|
| Application | For use in tap applications using large run and tap conductor sizes |
| Connector Type | Tap |
| Material | Copper |
| Sub Brand | WEJTAP |
| Trade Name | WEJTAP™ |
| Type | Wejtap Connector |
| UPC | 781810874400 |
| UPC 12 Digit | 7818108744000 |

Dimensions

| | |
|-------------------------------------------|---------|
| Dimension - F Width Center to Center inch | 3 in |
| Dimension - G inch | 1.53 in |

Conductor Related

| | |
|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - ACSR Str Run | 336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil;477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil |
| Conductor - ACSR Str Run Range | 336.4 (26/7) Linnet kcmil-556.5 (30/7) Eagle kcmil |
| Conductor - ACSR Str Tap | 336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil;477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil |
| Conductor - ACSR Str Tap Range | 336.4 (26/7) Linnet kcmil-556.5 (30/7) Eagle kcmil |
| Conductor - AL Str Run | 450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil |
| Conductor - AL Str Run Range | 450 kcmil-700 kcmil |
| Conductor - AL Str Tap | 450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil |
| Conductor - AL Str Tap Range | 450 kcmil-700 kcmil |

| | |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| Conductor Type | <ul style="list-style-type: none">• ACSR C Str-Run• AL C Str-Run• ACSR C Str-Tap• AL C Str-Tap |
|----------------|-----------------------------------------------------------------------------------------------------------------------------------------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 10 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)