

WCY62PB

by Burndy
Catalog ID: WCY62PB

Prop 65 Notice

Wejtap Assembly, 350 kcmil-700 kcmil (Run), 4/0 AWG-450 kcmil (Tap), Wiring taps.

Features: With Yellow Power Booster, ANSI Class AA, Installation Tool: WTRB, WTY Tool, Conductor Size (tap - Mm): 15 - 19 SQ-MM, Color Code: Yellow, Booster: WPBY Box 25, Booster Color: Yellow, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (run): 0.683 - 0.94 IN, Conductor Size (run - Mm): 17 - 24 SQ-MM, Cable Diameter Range (tap): 0.573 - 0.75 IN



Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Color	Yellow
Connector Type	Tap
Material	Copper
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector with Booster
UPC	781810870563
UPC 12 Digit	7818108705633

Dimensions

Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.53 in

Conductor Related

Conductor - ACSR Str Run	336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil;397.5 (26/7) Ibis kcmil;397.5 (30/7) Larkspur kcmil;477.0 (18/1) Pelican kcmil;477.0 (24/7) Flicker kcmil;477.0 (26/7) Hawk kcmil;477. (30/7) Hen kcmil;500.0 (30/7) Heron kcmil;556.5 (24/7) Parakeet kcmil;556.5 (26/7) Dove kcmil;556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Run Range	336.4 (18/1) Merlin kcmil-556.5 (30/7) Eagle kcmil
Conductor - ACSR Str Tap	4/0 (6/1) Penguin AWG;80 (8/1) Grouse kcmil;101.8 (12/7) Petrel kcmil;110.8 (12/7) Minorca kcmil;134.6 (12/7) Leghorn kcmil;159 (12/7) Guinea kcmil;176.9 (12/7) Dotterel kcmil;190.8 (12/7) Dorking kcmil;211.3 (12/7) Cochin kcmil;203.2 (16/9) Brahma kcmil;266.8 (18/1) Waxwing kcmil;266.8 (26/7) Owl kcmil;266.8 (26/7) Partridge kcmil;300.0 (26/7) Ostrich kcmil;336.4 (18/1) Merlin kcmil;336.4 (26/7) Linnet kcmil;336.4 (30/7) Oriole kcmil;397.5 (18/1) Chickadee kcmil;397.5 (24/7) Brant kcmil
Conductor - ACSR Str Tap Range	4/0 (6/1) Penguin AWG-397.5 (24/7) Brant kcmil
Conductor - AL Str Run	350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil
Conductor - AL Str Run Range	350 kcmil-700 kcmil
Conductor - AL Str Tap	4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil

Conductor - AL Str Tap Range	4/0 AWG-450 kcmil
Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Run• AL C Str-Run• ACSR C Str-Tap• AL C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	NC

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)