

WCY71PB

by Burndy
Catalog ID: WCY71PB

Prop 65 Notice

WEJTAP Connector, 1.133 - 0.907 (Run), 1.156 - 0.947 (Tap), With Yellow Power Booster Assembly



Product Details

General

Color	Yellow
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810870655
UPC 12 Digit	7818108706555

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.9 in

Conductor Related

Conductor - ACSR Str Run	477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Tap	556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard;874.5 (54/7) Crane;900 (54/7) Canary
Conductor - ACSR Str Tap Range	556.5 (26/7) Dove-900 (54/7) Canary
Conductor - AL Str Run	600;636;650;700;715.5;750;795.5;800;874.5;900;954;1000
Conductor - AL Str Run Range	600-1000
Conductor - AL Str Tap	650;700;715.5;750;795.5;800;874.5;900;954;1000;1033.5;1192.5;1272.2
Conductor - AL Str Tap Range	650-1272.2
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)