

WCY77

by Burndy
Catalog ID: WCY77

Prop 65 Notice

Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.829 (Max), 1.677 (Min).

Features: With Yellow Power Booster, ANSI Class AA, Color Code: Yellow, Booster Color: Yellow, Booster: WPBY Box 25, Conductor Size (tap - Mm): 15 - 19 SQ-MM, Installation Tool: WTRB, WTY Tool, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Cable Diameter Range (run): 0.889 - 1.133 IN, Conductor Size (run - Mm): 23 - 29 SQ-MM, Cable Diameter Range (tap): 0.575 - 0.75 IN



Product Details

General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810875254
UPC 12 Digit	7818108752544

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.9 in

Conductor Related

Conductor - ACSR Str Run	477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Tap	4/0 (6/1) Penguin;80 (8/1) Grouse;101.8 (12/7) Petrel;110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;203.2 (16/9) Brahma;211.3 (12/7) Cochin;266.8 (18/1) Waxwing;266.8 (26/7) Owl;266.8 (26/7) Partridge;300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole;397.5 (18/1) Chickadee;397.5 (24/7) Brant
Conductor - ACSR Str Tap Range	4/0 (6/1) Penguin-397.5 (24/7) Brant
Conductor - AL Str Run	556.5;600;636;650;700;715.5;750;795.5;800;874.5;900;954;1000
Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Tap	250;266.8;300;336.4;350;397.5;400;450
Conductor - AL Str Tap Range	250-450

Conductor Type	<ul style="list-style-type: none">• ACSR C Str-Run• AL C Str-Run• ACSR C Str-Tap• AL C Str-Tap
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)