

# WCY80PB

by Burndy  
Catalog ID: WCY80PB

Prop 65 Notice

Wejtap connector installed with Yellow booster, .889-.1133 Run, .364-.608 (Tap), Quantity: 5 Connectors per Box



## Product Details

### General

Color	Yellow
Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810870747
UPC 12 Digit	7818108707477

### Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.79 in

### Conductor Related

Conductor - ACSR Str Run	477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Tap	1 (6/1) Robin;1/0 (6/1) Raven;2/0 (6/1) Quail;3/0 (6/1) Pigeon;4/0 (6/1) Penguin;80 (8/1) Grouse;101.8 (12/7) Petrel;110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;203.2 (16/9) Brahma;211.3 (12/7) Cochin;266.8 (18/1) Waxwing
Conductor - ACSR Str Tap Range	1 (6/1) Robin-266.8 (18/1) Waxwing
Conductor - AL Str Run	556.5;600;636;650;700;715.5;750;795.5;800;874.5;900;954;1000
Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Tap	1;1/0;2/0;3/0;4/0;250;266.8;300
Conductor - AL Str Tap Range	1-300
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

## Logistics

Minimum Pack Quantity	5
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)