

# WCY83

by Burndy  
Catalog ID: WCY83

Prop 65 Notice

Wejtap Assembly , Installed With Yellow Booster, Sum of diameters: 1.440 (Max), 1.288 (Min).

Features: With Yellow Power Booster, ANSI Class AA, Installation Tool: WTRB Tool, Booster Color: Yellow, Conductor Size (tap - Mm): 7 - 10 SQ-MM, Color Code: Yellow, Booster: WPBY Box 25, Cable Diameter Range (run): 0.889 - 1.133 IN, Conductor Type: Run: ACSR, AAC, Tap: ACSR, AAC, Copper, Conductor Size (run - Mm): 23 - 29 SQ-MM, Cable Diameter Range (tap): 0.257 - 0.398 IN



## Product Details

### General

Application	For use in tap applications using large run and tap conductor sizes
Connector Type	Tap
Material	Aluminum
Sub Brand	WEJTAP
Trade Name	WEJTAP™
Type	Wejtap Connector
UPC	781810875551
UPC 12 Digit	7818108755511

### Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.79 in

### Conductor Related

Conductor - ACSR Str Run	477.0 (30/7) Hen;556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard
Conductor - ACSR Str Run Range	477.0 (30/7) Hen-795 (30/19) Mallard
Conductor - ACSR Str Tap	4 (7/1) Swanate;3 (6/1) Swallow;2 (6/1) Sparrow;2 (7/1) Sparate;1 (6/1) Robin;1/0 (6/1) Raven
Conductor - ACSR Str Tap Range	4 (7/1) Swanate-1/0 (6/1) Raven
Conductor - AL Str Run	556.5;600;636;650;700;715.5;750;795.5;800;874.5;900;954;1000
Conductor - AL Str Run Range	556.5-1000
Conductor - AL Str Tap	4;3;2;1;1/0;2/0
Conductor - AL Str Tap Range	4-2/0
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Run</li> <li>• AL C Str-Run</li> <li>• ACSR C Str-Tap</li> <li>• AL C Str-Tap</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	5
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)