

WCY95

by Burndy
Catalog ID: WCY95

Prop 65 Notice

Wejtap Assembly, 1.250-0.893 (Run), 0.722-0.525 (Tap), Installed With yellow Booster



Product Details

General

Connector Type	Tap
Material	Aluminum
Trade Name	WEJTAP™
UPC	781810876152
UPC 12 Digit	7818108761522

Dimensions

Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.96 in

Conductor Related

Conductor - ACSR Str Run	556.5 (24/7) Parakeet;556.5 (26/7) Dove;556.5 (30/7) Eagle;605 (24/7) Peacock;605 (26/7) Squab;605 (30/19) Teal;636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret;666.6 (24/7) Flamingo;715.5 (54/7) Crow;715.5 (26/7) Starling;715.5 (30/19) Redwing;795 (54/7) Condor;795 (26/7) Drake;795 (30/19) Mallard;874.5 (54/7) Crane;900 (54/7) Canary;954 (54/7) Cardinal;1033.5 (54/7) Curlew
Conductor - ACSR Str Run Range	556.5 (24/7) Parakeet-1033.5 (54/7) Curlew
Conductor - ACSR Str Tap	4/0 (6/1) Penguin;80 (8/1) Grouse;101.8 (12/7) Petrel;110.8 (12/7) Minorca;134.6 (12/7) Leghorn;159 (12/7) Guinea;176.9 (12/7) Dotterel;190.8 (12/7) Dorking;203.2 (16/9) Brahma;211.3 (12/7) Cochin;266.8 (18/1) Waxwing;266.8 (26/7) Owl;266.8 (26/7) Partridge;300.0 (26/7) Ostrich;336.4 (18/1) Merlin;336.4 (26/7) Linne
Conductor - ACSR Str Tap Range	4/0 (6/1) Penguin-336.4 (26/7) Linne
Conductor - AL Str Run	600;636;650;700;715.5;750;795.5;800;874.5;900;954;1000
Conductor - AL Str Run Range	600-1000
Conductor - AL Str Tap	4/0;250;266.8;300;336.4;350
Conductor - AL Str Tap Range	4/0-350
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Run • AL C Str-Run • ACSR C Str-Tap • AL C Str-Tap

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	5
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)