


WSL11

by Burndy
Catalog ID: WSL11

Prop 65 Notice

Stirrup assembly, 636 kcmil.

Features: Run Conductor position is identified on all wedges via a distinct chamfer, Conductor Type: Run: ACAR, Alumoweld, Copper (Compact Or Compressed), Galvanized Steel, ACSR (Compact Or Compressed), AAAC, Copperweld, ASC, AWAC, AAC (Standard), ACSR (Standard), Cable Diameter Range: 1.394 - 1.304 IN, Cable Diameter Range (run): 119 - 0.929 IN, Cable Diameter Range (tap): 0.375 IN, Bail Size: 2/0 AWG, Installation Tool: WTRBYK, Booster: WPBY Box 25



Product Details

General

Application	For common ACSR, Aluminium and Copper conductors
Color	Yellow
Material	Aluminum
Physical Attribute - Number of Holes	1
Sub Brand	WEJTAP, STIRRUP
Trade Name	WEJTAP™
Type	Wejtap with Stirrup
UPC	781810877609
UPC 12 Digit	7818108776099

Dimensions

Dimension - Bail Size	2/0
Dimension - F Width Center to Center inch	3.5 in
Dimension - G inch	1.83 in
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.4 in

Conductor Related

Conductor - ACSR Str Size	636 (24/7) Rook;636 (26/7) Grosbeak;636 (30/19) Egret
Conductor - ACSR Str Size Range	636 (24/7) Rook-636 (30/19) Egret
Conductor - AL Str Size	636
Conductor - AL Str Size Range	636
Conductor - Copper Str Size	636
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)