


# WSL1PB

by Burndy  
Catalog ID: WSL1PB

Prop 65 Notice

Wejtap large stirrup, .603-.726 (Run), .324-.324 (Tap).

Features: Run Conductor Position Is Identified On All Wedges Via A Distinct Chamfer, Color Code: Yellow, Booster: WPBY Box 25, Installation Tool: WTRBYK Tool, Conductor Type: ACAR, ALUMOWELD, Copper (Compact Or Compressed), Galvanized Steel, ACSR (Compact Or Compressed), AAAC, Copperweld, ASC, SOLID (Copper Or Aluminum), AWAC, AAC (Standard), ACSR (Standard), Cable Diameter Range (run): 0.603 - 0.726 IN, Cable Diameter Range (tap): 0.324 - 0.324 IN, Bail Size: 1/0 AWG



## Product Details

### General

Application	For Common ACSR, Aluminum And Copper Conductors
Color	Yellow
Material	Aluminum
Sub Brand	WEJTAP, STIRRUP
Trade Name	WEJTAP™
Type	Wejtap with Stirrup and Booster
UPC	781810871157
UPC 12 Digit	7818108711577

### Dimensions

Dimension - Bail Size	1/0
Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.32 in

### Conductor Related

Conductor - ACSR Str Size	336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - AL Str Size	336.4
Conductor - Copper Str Size	336.4

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	NC
UL Listed	No

### Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)