


## WSL2

by Burndy  
Catalog ID: WSL2

Prop 65 Notice

Stirrup Assembly, Large stirrups,Run:.726-.603,Tap:.375-.375.

Features: Run Conductor Position Is Identified On All Wedges Via A Distinct Chamfer, Installation Tool: WTRBYK Tool, Color Code: Yellow, Booster: WPBY Box 25, Conductor Type: ACAR, ALUMOWELD, Copper (Compact Or Compressed), Galvanized Steel, ACSR (Compact Or Compressed), AAAC, Copperweld, ASC, SOLID (Copper Or Aluminum), AWAC, AAC (Standard), ACSR (Standard), Cable Diameter Range (run): 0.603 - 0.726 IN, Cable Diameter Range (tap): 0.25 - 0.25 IN, Bail Size: 2/0 AWG



## Product Details

### General

Application	For Common ACSR, Aluminum And Copper Conductors
Color	Yellow
Material	Aluminum
Physical Attribute - Number of Holes	1
Sub Brand	WEJTAP, STIRRUP
Trade Name	WEJTAP™
Type	Wejtap with Stirrup
UPC	781810877159
UPC 12 Digit	7818108771599

### Dimensions

Dimension - Bail Size	2/0
Dimension - F Width Center to Center inch	3 in
Dimension - G inch	1.32 in
Dimension - Hole Size fraction	2/5
Dimension - Hole Size inch	0.4 in

### Conductor Related

Conductor - ACSR Str Size	336.4 (18/1) Merlin;336.4 (26/7) Linnet;336.4 (30/7) Oriole
Conductor - ACSR Str Size Range	336.4 (18/1) Merlin-336.4 (30/7) Oriole
Conductor - AL Str Size	336.4
Conductor - AL Str Size Range	336.4
Conductor - Copper Str Size	336.4
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

## Logistics

Minimum Pack Quantity	5
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)