


WSS1

by Burndy
Catalog ID: WSS1

Prop 65 Notice

Stirrup assembly, 6 kcmil.

Features: Run Conductor Position Is Identified On All Wedges Via A Distinct Chamfer, Installation Tool: WTRBYK Tool, Color Code: Red, Booster: WPBR Box 25, Conductor Type: ACAR, ALUMOWELD, Copper (Compact Or Compressed), Galvanized Steel, ACSR (Compact Or Compressed), AAAC, Copperweld, ASC, SOLID (Copper Or Aluminum), AWAC, AAC (Standard), ACSR (Standard), Cable Diameter Range (run): 0.162 - 0.204 IN, Bail Size: 2 AWG, Cable Diameter Range (tap): 0.25 - 0.25 IN



Product Details

General

Application	For Common ACSR, Aluminum And Copper Conductors
Material	Aluminum
Physical Attribute - Number of Holes	1
Sub Brand	WEJTAP, STIRRUP
Trade Name	WEJTAP™
Type	Wejtap with Stirrup
UPC	781810876657
UPC 12 Digit	7818108766577

Dimensions

Dimension - Bail Size	2
Dimension - F Width Center to Center inch	1.4 in
Dimension - G inch	0.92 in
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in

Conductor Related

Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - ACSR Str Size Range	6 (6/1) Turkey AWG
Conductor - AL Str Size	6 AWG
Conductor - AL Str Size Range	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor - Copper Str Size Range	6 AWG
Conductor Type	<ul style="list-style-type: none"> • ACSR C Str-Size • AL C Str-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)