


## WSS2

by Burndy  
Catalog ID: WSS2

Prop 65 Notice

Stirrup Assembly, Small stirrups.

Features: Run Conductor Position Is Identified On All Wedges Via A Distinct Chamfer, Installation Tool: WTRBYK Tool, Color Code: Red, Booster: WPBR Box 25, Conductor Type: ACAR, ALUMOWELD, Copper (Compact Or Compressed), Galvanized Steel, ACSR (Compact Or Compressed), AAAC, Copperweld, ASC, SOLID (Copper Or Aluminum), AWAC, AAC (Standard), ACSR (Standard), Cable Diameter Range (run): 0.206 - 0.325 IN, Cable Diameter Range (tap): 0.25 - 0.25 IN, Bail Size: 2 AWG



## Product Details

### General

Application	For Common ACSR, Aluminum And Copper Conductors
Material	Aluminum
Physical Attribute - Number of Holes	1
Sub Brand	WEJTAP, STIRRUP
Trade Name	WEJTAP™
Type	Wejtap with Stirrup
UPC	781810876701
UPC 12 Digit	7818108767011

### Dimensions

Dimension - Bail Size	2
Dimension - F Width Center to Center inch	1.4 in
Dimension - G inch	0.92 in
Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in

### Conductor Related

Conductor - ACSR Str Size	5 (6/1) Thrush AWG;4 (6/1) Swan AWG;4 (7/1) Swanate AWG;3 (6/1) Swallow AWG;2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	5 (6/1) Thrush AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	4 AWG;3 AWG;2 AWG
Conductor - AL Str Size Range	4 AWG-2 AWG
Conductor - Copper Str Size	5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Str Size Range	5 AWG-2 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• ACSR C Str-Size</li> <li>• AL C Str-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Standards - RoHS Compliance Status
------------------------------------

CM
----

## Logistics

Minimum Pack Quantity
-----------------------

10
----

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)