

XP2020

by Burndy
Catalog ID: XP2020

Prop 65 Notice

Cast Copper Alloy Expansion Coupler , 3 IN IPS, 13.50 IN L



Product Details

General

Application	Substation
Connector Type	Couplers
Installation Torque Recommended in-lb	660 in-lb
Material	Copper Alloy
Material - Hardware	DURIUM™ Silicon Bronze
One Wrench Installation	Y
Physical Attribute - Number of Run Conductors	1
Physical Attribute - Number of Tap Conductors	1
Physical Attribute - Pad Orientation	Straight
Plated	N
Plating Type	Unplated
Type	Tube to Tube Couplers
UPC	781810005095
UPC 12 Digit	7818100050955

Dimensions

Dimension - Height inch	7.75 in
Dimension - L Length Overall mm	343 mm
Dimension - Length BB inch	4.00 in
Dimension - Length Overall inch	13.50 in

Electrical Ratings

Rating - KVA	230 kV
--------------	--------

Conductor Related

Conductor - Connection Combination	Tube to Tube
Conductor - Copper Tube Std Size	3 IPS
Conductor - Copper Tube Std Size Range	3 IPS
Conductor Type	CU Tube Std-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)