

Y262CR

by Burndy
Catalog ID: Y262CR

Cu Comp Reducer Adapter Sleeve Code Cond, 2/0-2 Str, 600 V-35 kV, 1.50
" L, Tin Plated, For Cu.



Product Details

General

Connector Type	Reducer
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
UPC	781810030905
UPC 12 Digit	7818100309055

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.50 in
Dimension - Outside Diameter inch	0.43 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	2/0 AWG
Conductor - Copper Str Run Range	2/0 AWG
Conductor - Copper Str Tap	2 AWG
Conductor - Copper Str Tap Range	2 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)