

Y281CR

by Burndy
Catalog ID: Y281CR

Prop 65 Notice

Cu Reducer Adapter Sleeves, 4/0 STR to #1 STR, Tin Plated, Compression



Product Details

General

Connector Type	Reducer
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
UPC	781810000977
UPC 12 Digit	7818100009777

Dimensions

Dimension - B Length inch	1.75 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	0.534 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Tap	1 AWG
Conductor - Copper Str Tap Range	1 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)