

## Y284CR

by Burndy  
Catalog ID: Y284CR

Prop 65 Notice

Cu Reducer Adapter Sleeves, 4/0 STR to #4 STR, Tin Plated, Compression



## Product Details

### General

Connector Type	Reducer
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
UPC	781810000991
UPC 12 Digit	7818100009911

### Dimensions

Dimension - B Length inch	1.75 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.75 in
Dimension - Outside Diameter inch	0.534 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Run	4/0 AWG
Conductor - Copper Str Run Range	4/0 AWG
Conductor - Copper Str Tap	4 AWG
Conductor - Copper Str Tap Range	4 AWG

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Carton Quantity	100 EA
Minimum Pack Quantity	25

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)