

Y2C6CR

by Burndy
Catalog ID: Y2C6CR

Prop 65 Notice

Copper Compression Reducing Adapter, 2 STR - 6 STR AWG, 1.25" Long, Tin Plated.



Product Details

General

Connector Type	Reducer
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
UPC	781810098554
UPC 12 Digit	7818100985544

Dimensions

Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Inside Diameter inch	0.2 in
Dimension - Outside Diameter inch	0.293 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	2 AWG
Conductor - Copper Str Run Range	250 kcmil
Conductor - Copper Str Tap	6 AWG
Conductor - Copper Str Tap Range	4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed	No
-----------	----

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)