

Y3027R

by Burndy
Catalog ID: Y3027R

Prop 65 Notice

Copper Compression Reducing Adapter, 300 kcmil - 3/0 STR AWG, 2.0" Long, Tin Plated.



Product Details

General

Connector Type	Reducer
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
UPC	781810121221
UPC 12 Digit	7818101212211

Dimensions

Dimension - B Length inch	2.00 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in
Dimension - Outside Diameter inch	0.637 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	300 kcmil
Conductor - Copper Str Run Range	300 kcmil
Conductor - Copper Str Tap	3/0 AWG
Conductor - Copper Str Tap Range	3/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM

UL Listed

No

Logistics

Minimum Pack Quantity

100

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)