

Y3129R

by Burndy
Catalog ID: Y3129R

Prop 65 Notice

Cu Reducer Adapter Sleeves, 350 kcmil-250 kcmil Code, 600V-35kV, Tin Plated, Compression.

Accommodates wide range of conductors, provides maximum conductivity, ductility and long lasting corrosion resistance



Product Details

General

Application	FOR COPPER
Connector Type	Reducer
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin Plated
Sub Brand	REDUCER SPLICES
Temperature Rating	194
Type	Y-R
UPC	781810081938
UPC 12 Digit	7818100819388

Dimensions

Dimension - B Length inch	2.00 in
Dimension - L Length Overall mm	51 mm
Dimension - Length Overall inch	2.00 in
Dimension - Outside Diameter inch	0.687 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	350 kcmil
Conductor - Copper Str Run Range	350 kcmil
Conductor - Copper Str Tap	250 kcmil
Conductor - Copper Str Tap Range	250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)