

# Y3425R

by Burndy  
Catalog ID: Y3425R

Prop 65 Notice

Copper Compression Reducing Adapter, 500 kcmil - 1/0 STR AWG, 2.50" Long, Tin Plated.



## Product Details

### General

Connector Type	Reducer
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
UPC	781810001042
UPC 12 Digit	7818100010422

### Dimensions

Dimension - B Length inch	2.50 in
Dimension - L Length Overall mm	64 mm
Dimension - Length Overall inch	2.50 in
Dimension - Outside Diameter inch	0.821 in

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Run	500 kcmil
Conductor - Copper Str Run Range	500 kcmil
Conductor - Copper Str Tap	1/0 AWG
Conductor - Copper Str Tap Range	1/0

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

## Logistics

Minimum Pack Quantity	50
-----------------------	----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)