

Y342CR

by Burndy
Catalog ID: Y342CR

Prop 65 Notice

Copper Compression Reducing Adapter, 500 kcmil - #2 STR AWG, 2.50" Long, Tin Plated.



Product Details

General

| | |
|-----------------------|----------------------|
| Connector Type | Reducer |
| Feature - Barrel Type | Long |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin - Electro Plated |
| Temperature Rating | 194 |
| UPC | 781810001004 |
| UPC 12 Digit | 7818100010044 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length inch | 2.50 in |
| Dimension - L Length Overall mm | 64 mm |
| Dimension - Length Overall inch | 2.50 in |
| Dimension - Outside Diameter inch | 0.821 in |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|-----------------------------------|-----------|
| Conductor - Copper Str Run | 500 kcmil |
| Conductor - Copper Str Size | 2 AWG |
| Conductor - Copper Str Size Range | 2 AWG |
| Conductor - Copper Str Tap | 2 AWG |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)