

Y35BH

by Burndy
Catalog ID: Y35BH

Prop 65 Notice

Remote Power Operated Crimping Tool Head, 12 Ton, 10000 psi, 8 AWG(Sol) - 750 kcmil Copper, 6 AWG(Sol) - 750 kcmil Aluminium, U Dies.

- Lifting eye
- 0.95" jaw opening
- Uses U style dies
- Positive die lock buttons

Easy tool removal from line conductor after compression taps are installed with the open C shaped head, Easily lifted into working position using the lifting eye, Long life expectancy is provided with heavy duty reinforced back 5 year limited warranty



Product Details

General

Application	For Use On: 8 AWG Solid - 500 KCMIL Copper, 6 AWG Solid - 636 KCMIL Aluminum, 4 AWG - 556.5 KCMIL 26/7 Stranded, 14 AWG - 556.5 KCMIL ACSR (18/1), 6 AWG Stranded - 500 KCMIL Copper, 4 AWG Stranded - 600 KCMIL Aluminum, Code Conductors 8 AWG Stranded - 750 KCMIL Copper (Terminals), 400 KCMIL Copper (Splices), 6 AWG Stranded - 750 KCMIL Aluminum (Terminals), 400 KCMIL Aluminum (Splices), HYGROUND Compression Grounding, 6 AWG - 250 KCMIL Copper (Cable/Ground Rod), 1/2 - 3/4 IN Ground Rods
Crimp Force Capacity	12 ton
Sub Brand	HYPRESS
Tool Type	Remote Hydraulic Crimp Head
Trade Name	HYPRESS™
Type	Crimpers
UPC	781810408452
UPC 12 Digit	7818104084522

Dimensions

Dimension - Length Overall inch	9.75 in
Height	9.25 in
Jaw Width	0.95 in
Length	2.62 in
Weight	8 lb
Width	4.75 in

Conductor Related

Crimping Ranges	Copper #8 str. - 500 kcmil code cable (Grounding Terminals, Grounding Splices); Copper #8 str. - 500 kcmil and up to 3/4" ground rod (Grounding Taps); Copper #8 str. - 750 kcmil code cable, N30 - N500 Navy cable, flexible, and extra flex (Terminals (Bare), Terminals (Insulated), Splices to 400 kcmil only); Aluminum #8 str. - 750 kcmil code cable (Terminals, Splices to 350 kcmil only)
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)