

Y3936R

by Burndy
Catalog ID: Y3936R

Prop 65 Notice

Cu Comp Reducer Adapter Sleeve Code Cond, 750-600 kcmil, 600 V-35 kV, 2.88 " L, Tin Plated, For Cu.

Wide range of conductors are accommodated, Length fits the long barrel connector design (YS, YA), Can be used on all long barrel connectors. Field cut to fit shorter length compression barrels (YS-L, YA-L), Manufactured from high conductivity electrolytic copper and electro-tin plated



Product Details

General

Application	Reducer
Connector Type	Reducer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	REDUCER/ADAPTER
Temperature Rating	194
Type	Y-R, Compression
UPC	781810081921
UPC 12 Digit	7818100819211

Dimensions

Dimension - B Length inch	2.06 in
Dimension - Inside Diameter inch	0.92 in
Dimension - L Length Overall mm	73 mm
Dimension - Length Overall inch	2.88 in
Dimension - Outside Diameter inch	1.017 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	750 kcmil
Conductor - Copper Str Size	600 kcmil
Conductor - Copper Str Size Range	600 kcmil
Conductor - Copper Str Tap	600 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)