

Y4439R

by Burndy
Catalog ID: Y4439R

Prop 65 Notice

Copper Compression Reducing Adapter, 1000 kcmil - 750 kcmil STR
AWG, 3.00" Long, Tin Plated.



Product Details

General

Connector Type	Reducer
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
UPC	781810085905
UPC 12 Digit	7818100859055

Dimensions

Dimension - B Length inch	3.00 in
Dimension - Inside Diameter inch	1.03 in
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	3.00 in
Dimension - Outside Diameter inch	1.159 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	1000 kcmil
Conductor - Copper Str Run Range	1000 kcmil
Conductor - Copper Str Tap	750 kcmil
Conductor - Copper Str Tap Range	750 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)