

Y46LWSBH

by Burndy
Catalog ID: Y46LWSBH

Prop 65 Notice

Hypress Tool, Supplied with Male Hydraulic Coupler.

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter
- Positive push button die locks
- Light weight scoop style open head design
- Lead Time :12 Days

Lead Time :125 year limited warranty



Product Details

General

Application	Used with Y46LWBH
Crimp Force Capacity	15 ton
Die Type	P style and U style with PUADP1 adapter
Sub Brand	CRIMPER - REMOTE HYDRAULIC
Tool Type	Remote Hydraulic Crimp Head
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810673713
UPC 12 Digit	7818106737133

Dimensions

Height	14.68 in
Length	14.68 in
Weight	14.5 lb

Conductor Related

Crimping Ranges	Copper - #8 AWG Str. - 1500 kcmil; Aluminum - #8 AWG - 1250 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)